

Fiber, Pigtail, Bundle, LC-Single Mode, 12-Fiber Strands, OS2 Fiber, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPBKR12LC6S](#)

Fiber, Pigtail, Bundle, LC-Single Mode, 12-Fiber Strands, OS2
Fiber, 3 Meter Length

Features

- Bundle
- LC-Single Mode
- 12-Fiber Strands
- OS2 Fiber
- 3 Meter Length

Application

Optical Signal

Conductor

Conductor Type	Glass
Wire Type	Multimode
Wire Size	9 Micron

Current

Connectivity	Plug-In
--------------	---------

Dimensions

Length	118.11 in
Pitch	12

Outside Diameter	0.2
------------------	-----

General

Color	Yellow
UPC	662620363240
Plug Type	LC-SM, 12F, OS2
Material	Glass Fiber
Material - Jacket	Flame Redardant PVC
Material - Insulation	Flame Redardant PVC

Logistics

Carton Quantity	50
-----------------	----

Operational

Temperature Rating	TIA 568-C.3
--------------------	-------------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)