

Fiber Optic Pigtail, LC Single Mode,
10GbE, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPLCE3MM](#)

Fiber Optic Pigtail, LC Single Mode, 10GbE, 3 Meter Length

Features

- 10GbE
- 3 Meter Length

Application

LC

General

Catalog Number	FHPLCE3MM
Color	Aqua
Connector Type	LC
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363523

Dimensions

Display Size	50 Micron, OM3
Length (Meters)	3 m



Pitch	6
-------	---

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OM3, MM
Wire Type	Multimode

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Catalog Page - PREM H7 Catalog Page](#)
- [Catalog Page - PREM H08 Catalog Page](#)
- [Catalog Page - PREM H8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - FiberHUBB™ Series Pigtails](#)
- [Sales Drawings - FPLCE3MM - PDF](#)
- [Specifications - FHPLCE3MM](#)