

Fiber Optic, Pigtail, LSZH, LC,
50Micron, 125 Multi Mode, OM4, 3
Meter Length

By Hubbell Premise Wiring
Catalog # [FHPLCF3MM](#)

Fiber Optic, Pigtail, LSZH, LC, 50Micron, 125 Multi Mode, OM4, 3
Meter Length

Features

- LSZH
- LC
- 50Micron
- 125 Multi Mode
- OM4

Application

LC

General

Catalog Number	FHPLCF3MM
Color	Aqua
Connector Type	LC
Construction Material - Main	Glass Fiber
Insulation	PVC
Size	OM4
Sub Brand	Fiber Optic Products
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363554

Dimensions



Length (Meters)3 m

Conductor Related

ModeOM4, MM
Wire TypeMultimode

Certifications And Compliance

Industry Standard(s)TIA 568C.4

Logistics

Carton Quantity50

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Catalog Page - PREM H7 Catalog Page](#)
- [Catalog Page - PREM H08 Catalog Page](#)
- [Catalog Page - PREM H8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - FiberHUBB™ Series Pigtails](#)
- [Sales Drawings - FPLCF3MM - PDF](#)
- [Specifications - FHPLCF3MM](#)