

Fiber Optic Pigtail, LC Single Mode,
3) Meter Length

By Hubbell Premise Wiring
Catalog # [FHPLCS3SM](#)



Fiber Optic Pigtail, LC Single Mode, 3) Meter Length

Features

3) Meter Length

Application

LC

General

Catalog Number	FHPLCS3SM
Color	Yellow
Connector Type	LC
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363578

Dimensions

Display Size	SM, OS2
Length (Meters)	3 m

Pitch	6
-------	---

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OS2, SM
Wire Type	Singlemode

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Catalog Page - PREM H7 Catalog Page](#)
- [Catalog Page - PREM H08 Catalog Page](#)
- [Catalog Page - PREM H8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - FiberHUBB™ Series Pigtails](#)
- [Sales Drawings - FPLCS3SM - PDF](#)
- [Specifications - FHPLCS3SM](#)