

FIBERHUBB™

Trunks

MPO Hydra Cable Assembly

HUBBELL

Features

- Factory terminated and tested for simple installation
- Customizable length, color, strand count and cable construction
- Easily migrate to 40G, 100G, 200G, and beyond
- Premium low loss connector options for all applications
- Built with Corning ClearCurve Fiber and assembled in the USA

Ordering Information

Description	Color	Catalog No.	UPC
FIBERHUBB Plenum MPO Hydra Trunk Assembly, OM4, 12-Strand, 10 Feet	Aqua	FHPMPLCM4L10FN	662620368764

Listings

ANSI/TIA-568.3-D; IEEE 802.3
IEC 61300-3-35
GR-326
RoHS; UL 94 V-0; NFPA 262

Specifications

Cable	Plenum Loose Tube Micro Distribution
Jacket	Flame Retardant PVC
Connector End A	MPO Plus Premium Low Loss Mini
Connector End B	LC Unibody Mini Boot
Link Length	550 (10Gb)
Applications	IEEE 802.3, 40GBASE-ER4; 100GBASE-LR4

Performance

Insertion Loss

(Typical / Max) (0.10 / 0.30)

Mating Durability

500 cycles

Max Attenuation

(dB/km) 3.0 / 1.0

Return Loss

= 25



Accessories

12-Port Cassette	OCLC50G4
24-Port Cassette	OCLCD50G4
High Density H4 Cassette	OCLCQG4H4
UltraMax Frame	FHDV1U144LC12MP4
Adapter Panel	FSPNMTPAQ6

Online Resources

Customer Sales Drawings
eCatalog