

Fiber Optic Pigtail, SC Multi Mode, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPSCC3MM](#)

Fiber Optic Pigtail, SC Multi Mode, 3 Meter Length



Features

- 3 Meter Length

Application

SC

Conductor

Mode	OM1, MM
Wire Type	Multimode

Current

Connectivity	Plug-In
--------------	---------

Dimensions

Length (Meters)	3 m
Pitch	6

General

Color	Orange
UPC	662620363622
Material	Glass Fiber

Logistics

Carton Quantity	100
-----------------	-----

Operational

Temperature Rating	0 Degrees C to 75 Degree C
--------------------	----------------------------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)