

Fiber Optic Pigtail, SC Multi Mode, 10GbE,
3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPSC3MM](#)

Fiber Optic Pigtail, SC Multi Mode, 10GbE, 3 Meter Length



Features

- 10GbE
- 3 Meter Length

Application

SC

Conductor

Mode	OM3, MM
Wire Type	Multimode

Current

Connectivity	Plug-In
--------------	---------

Dimensions

Length (Meters)	3 m
Pitch	6

General

Color	Aqua
UPC	662620363646
Material	Glass Fiber

Logistics

Carton Quantity	50
-----------------	----

Operational

Temperature Rating	0 Degrees C to 75 Degree C
--------------------	----------------------------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)