

HUBBELL

Premise Wiring

Fiber Optic, Pigtail, LSZH, 50 Micron, 125, Multi Mode, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FHPSCF3MM](#)

Fiber Optic, Pigtail, LSZH, 50 Micron,125, Multi Mode, 3 Meter Length

Features

- LSZH
- 50 Micron
- 125
- Multi Mode
- 3 Meter Length

Application

SC

Specifications

Industry Standard(s) TIA 568C.5

Conductor

Mode OM4, MM
Wire Type Multimode

Dimensions

Length (Meters) 3 m



Size OM4

General

Color Aqua
UPC 662620363660
Type OptiChannel Fiber Pigtails, Single and Bundled Fiber Optic Products
Sub Brand

Logistics

Carton Quantity 50

Operational

Temperature Rating 0 Degrees C to 75 Degree C

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)