

Fiber Optic Pigtail, ST-Style Multi Mode, 3 Meter Length



By Hubbell Premise Wiring
Catalog # [FHPSTC3MM](#)

Fiber Optic Pigtail, ST-Style Multi Mode, 3 Meter Length

Features

3 Meter Length

Application

ST

General

Catalog Number	FHPSTC3MM
Color	Orange
Connector Type	ST
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620363707

Dimensions

Display Size	62.5 Micron, OM1
Length (Meters)	3 m

Pitch	6
-------	---

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OM1, MM
Wire Type	Multimode

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Catalog Page - PREM H7 Catalog Page](#)
- [Catalog Page - PREM H08 Catalog Page](#)
- [Catalog Page - PREM H8 CatalogPage](#)
- [Catalogs - Premise Wiring Catalog](#)
- [Literature - FiberHUBB™ Series Pigtails](#)
- [Sales Drawings - FPSTC - PDF](#)
- [Specifications - FHPSTC3MM](#)