

Fiber Optic Pigtail, LC Single Mode,
10GbE, 3 Meter Length

By Hubbell Premise Wiring
Catalog # [FPLCE3MM](#)



Fiber Optic Pigtail, LC Single Mode, 10GbE, 3 Meter Length

Application

LC

General

Catalog Number	FPLCE3MM
Connector Type	LC
EU RoHS Indicator	Yes
Insulation	PVC
Item Type	OptiChannel Fiber Pigtails, Single and Bundled
Material	Glass Fiber
Temperature Rating	0 Degrees C to 75 Degree C
UPC	662620200354

Dimensions

Display Size	50 Micron, OM3
Length (Meters)	3 m

Pitch	6
-------	---

Electrical Ratings

Connectivity	Plug-In
--------------	---------

Conductor Related

Mode	OM3, MM
Wire Type	Multimode

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

- [Brochures - Fiber Connectivity Product Guide](#)
- [Specifications - FPLCE3MM Specification Sheet French](#)
- [Specifications - FPLCE3MM Specification Sheet English](#)