

Pedestal, 2-Gang, Aluminum

By Hubbell Premise Wiring
Catalog # [FR280ALA](#)

FRPT Pedestal, Double



Features

- 1-4 hour fire rating (1-3 hour for steel floor units and concrete topping, D900 Series Design)
- For 2 1/4 in. to 7 in. floor thickness
- Approved for use in the City of Chicago

Application

Through Floor Delivery

Specifications

Industry Standard(s)	UL 514A
EU RoHS Indicator	No

Conductor

Cable Entry	Direct into Device
-------------	--------------------

Dimensions

Size	Standard Sized Product
------	------------------------

General

Mounting Hardware	Included
Sub Brand	Accessories

Material - Mounting Hardware	On PT27A Through Floor Fitting
Type	Above Floor Service Fittings
Material	Aluminum
Specifications	• Cubic Inch Capacity - 39.00 in. (638.8cm3) • Housing - Painted aluminum • Pedestal Finish - Textured black or gray epoxy paint • Power Capacity - 19.5 in. (319.4cm3) • Voice/Data - 19.5 in. (319.4cm3)
UPC	783585396231
Style	Pedestals
Color	Aluminum
Mounting Type	On PT27A or PT7XC Through Floor Fitting

Logistics

Carton Quantity	5
-----------------	---

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)