

HUBBELL

Premise Wir

[PlugTrak, Aluminum, Tamper Resistant, 20A125V, 3' Length, Anodized](#)

By Hubbell Premise Wiring

Catalog # [HBLALU24GB306TR](#)

PlugTrak, Tamper Resistant 20A125V, 3', Anodized



Features

- Tamper Resistant
- Available in 3ft. 5 ft. or 6 ft. lengths
- Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions
- Multiple spacing configurations
- Hubbell designed and manufactured 15 or 20 Amp receptacles

Specifications

EU RoHS Indicator
Contact Manufacturer

Configuration

Number Of Receptacles
6

Current

Current / Amperage Rating
20 A

Dimensions

Length
3 ft

General

Style
Tamper Resistant
UPC
783585453095
Type
Single Circuit
Series
Aluminum

Logistics

Carton Quantity
2

Product Assets

[Catalog.\[English\]](#)
[Catalog.\[English\]](#)
[Catalog Page.\[English\]](#)



A Hubbell brand
© 2026 Hubbell Incorporated. All rights reserved
PREM-HBLALU24GB306TR-SPEC-EN | REV 5/2026