

HUBBELL

Premise Wiring

PlugTrak, Aluminum, Tamper Resistant,
20A125V, 5' Length, Anodized



By Hubbell Premise Wiring
Catalog # [HBLALU24GB512TR](#)

PlugTrak, Tamper Resistant 20A125V, 5', Anodized

Features

- Tamper Resistant
- Available in 3ft. 5 ft. or 6 ft. lengths
- Available in Standard, Isolated Ground (IG), Tamper-Resistant (TR) and USB (U) versions
- Multiple spacing configurations
- Hubbell designed and manufactured 15 or 20 Amp receptacles

Specifications

EU RoHS Indicator Contact Manufacturer

Configuration

Number Of Receptacles 5

Current

Current / Amperage Rating 20 A

Dimensions

Length 5 ft

General

Style Tamper Resistant
UPC 783585453101
Type Single Circuit
Series Aluminum

Logistics

Carton Quantity 1

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)