

## Features

- Ceiling trim mounting plate and scuff boot included
- All conductors are #12 AWG stranded copper
- Ready for quick installation
- UL Listed

## Ordering Information

| Style  | Color/Finish | Catalog Number | UPC Number   |
|--|--------------|----------------|--------------|
| Blank pole with divider, 4 styleline knockouts | Ivory finish | HBLPPO12AI     | 783585345536 |



## Listings

UL Listed

## Characteristics

|                    |          |
|--------------------|----------|
| Ceiling Trim plate | Included |
| Divider            | Included |
| Scuff Boot         | Included |

## Dimensions- inches (mm)

|        |              |
|--------|--------------|
| Length | 12'2" (3710) |
| Width  | 2.13" (54)   |
| Depth  | 2.1" (54)    |

## Accessories

|                          |                |
|--------------------------|----------------|
| Adjustable T-bar bracket | <b>ATB</b>     |
| Replacement trim kit     | <b>PPTRIM1</b> |

## Online Resources

[Delivery Systems Guide](#)  
[eCatalog](#)  
[Product Drawing](#)  
[Service Poles Guide](#)