

HUBBELL Premise Wiring

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 5' Length, Gray

By Hubbell Premise Wiring
Catalog # [HC6AGY05](#)

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 5' Length,
Gray



Features

- Ascent
- Cat6A
- Slim
- 5' Length
- Gray

Application

Category 6A

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Conductor Stranding Stranded
Wire Size #24 AWG
Number Of Conductors 8-Conductor

Current

Voltage Rating 300V AC kV

Dimensions

Outside Diameter 0.218

General

Plug Type RJ45
OEM Brand Name Hubbell Premise Wiring
Material - Jacket Flame Redardant PVC
Material - Insulation Flame Redardant PVC
UPC 662620229898
Color Gray

Operational

Temperature Rating Per TIA

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)