

HUBBELL

Premise Wiring

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 25' Length, Gray

By Hubbell Premise Wiring
Catalog # [HC6AGY25](#)

Copper Solutions, Patch Cords, Ascent, Cat6A, Slim, 25' Length, Gray



Features

- Ascent
- Cat6A
- Slim
- 25' Length
- Gray

Application

Category 6A

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type	Copper
Conductor Stranding	Stranded
Number Of Conductors	8-Conductor
Wire Size	#24 AWG

Current

Voltage Rating 300V AC kV

Dimensions

Outside Diameter 0.218

General

Color	Gray
UPC	662620229942
Plug Type	RJ45
Material - Jacket	Flame Redardant PVC
Material - Insulation	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring

Operational

Temperature Rating Per TIA

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)