

OptiChannel  
Indoor/Outdoor Tight Buffer Cable  
Riser

HUBBELL

Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Ordering Information

| Description                                                                    | Fiber         | Catalog Number | UPC Number   |
|--------------------------------------------------------------------------------|---------------|----------------|--------------|
| 2 strand, OM4, MM, I/O Tight Buffer Riser, Indoor/Outdoor Tight Buffer - Black | OM4 Multimode | HFCD14002R4BK  | 662620555584 |



Listings

ANSI/ICEA S-83-596  
TIA-568.3-D  
NFPA-262/UL910/CSA FT-6  
Telcordia GR-409 and GR-20

Specifications

|                        |                                     |
|------------------------|-------------------------------------|
| Fiber Coating          | 900 Micron PVC Tight Buffer         |
| Cable Diameter in (mm) | 0.17 (4.4)                          |
| Cable Weight (lb/kft)  | 12                                  |
| Construction           | Single Unit, Aramid Strength Member |
| Armor                  | None                                |

Performance

Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

Maximum Installation Pulling Load (lb)

150

Maximum Operating Temperature

-4°F to +185°F (-20°C to +85°C)

Minimum Bend Radius, In-Service in (cm)

1.73 (4.4)

Accessories

|                           |             |
|---------------------------|-------------|
| Fiber Strip Tool          | OFSTRIP2    |
| Splice Tray, 12 Fusion    | STRAY12F    |
| Splice Tray, 24 Fusion    | STRAY24F    |
| Splice Protection Sleeves | FSHST401025 |

Online Resources

eCatalog