

OptiChannel  
Indoor Distribution Cable  
Riser



Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Durable Aluminum Interlock Armor
- Premium Fiber For Enhanced Optical Performance

Ordering Information

| Description                                                                 | Fiber         | Catalog Number | UPC Number   |
|-----------------------------------------------------------------------------|---------------|----------------|--------------|
| 24 strand, OM3, MM, Riser, Armored, Indoor Tight Buffer Distribution - Aqua | OM3 Multimode | HFCD15024R3    | 662620333779 |



Listings

ANSI/ICEA S-83-596  
TIA-568.3-D  
NFPA-262/UL910/CSA FT-6  
Telcordia GR-409 and GR-20

Specifications

|                        |                                     |
|------------------------|-------------------------------------|
| Fiber Coating          | 900 Micron PVC Tight Buffer         |
| Cable Diameter in (mm) | 0.69 (17.4)                         |
| Cable Weight (lb/kft)  | 188                                 |
| Construction           | Single Unit, Aramid Strength Member |
| A armor                | Aluminum Interlock                  |

Performance

Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

Maximum Installation Pulling Load (lb)

300

Maximum Operating Temperature

-4°F to +158°F (-20°C to +70°C)

Minimum Bend Radius, In-Service in (cm)

3.2 (8.1)

Accessories

|                           |             |
|---------------------------|-------------|
| Fiber Strip Tool          | OFSTRIP2    |
| Splice Tray, 12 Fusion    | STRAY12F    |
| Splice Tray, 24 Fusion    | STRAY24F    |
| Splice Protection Sleeves | FSHST401025 |

Online Resources

eCatalog

