

HFCD15 Series Indoor Tight Buffer
Distribution, 72 strand, Riser,
Armored, OM4, MM , Aqua Jacket

By Hubbell Premise Wiring
Catalog # [HFCD15072R4](#)

HFCD15 Series Indoor Tight Buffer Distribution, 72 strand, Riser,
Armored, OM4, MM , Aqua Jacket.

Features

- Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Durable Aluminum Interlock Armor
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

General

Attenuation	3.5/1.5 Db per Kilometer
Bandwidth	4000 bps
Cable Rating	Riser, Armored
Catalog Number	HFCD15072R4
Color	Aqua
Sub Brand	Fiber Optics
Temperature Rating	-10 Degrees C to 70 Degrees C
Type	Cable
UPC	662620343389



Electrical Ratings

Wavelength	850/1300 Nanometers
------------	---------------------

Conductor Related

Fiber Size	OM4
Fiber Type	OM4, MM
Number of Fibers	72

Certifications And Compliance

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-4 • Telcordia GR-409 • TIA-568.3-D
----------------------	---

Product Assets

[Literature - Fiber Optic Cable Guide](#)
[Specifications - HFCD15072R4](#)