

OptiChannel

Indoor Distribution Cable

Plenum




Features

- Corning ClearCurve® Multimode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- Compact Cable Diameter Reduces Pathway Congestion
- Premium Fiber For Enhanced Optical Performance

Ordering Information

Description	Fiber Type	Catalog No.	UPC
72 strand, OM3, MM, Plenum, Multi- Unit, Indoor Tight Buffer Distribution - Aqua	OM3 Multimode	HFCD1M12072P3	662620555614



Listings

ANSI/ICEA S-83-596
TIA-568.3-D
NFPA-262/UL910/CSA FT-6
Telcordia GR-409 and GR-20

Specifications

Fiber Coating	900 Micron PVC Tight Buffer
Cable Diameter in (mm)	0.79 (20)
Cable Weight (lb/kft)	238
Construction	Multi-Unit, 12F/Unit, Central Strength Member
Armor	None

Performance

Cable Attenuation (dB/km at 850/1300 nm)

3.5/1.5

Maximum Installation Pulling Load (lb)

600

Maximum Operating Temperature

-4°F to +158°F (-20°C to +70°C)

Minimum Bend Radius, In-Service in (cm)

7.9 (20)

Accessories

Fiber Strip Tool	OFSTRIP2
Splice Tray, 12 Fusion	STRAY12F
Splice Tray, 24 Fusion	STRAY24F
Splice Protection Sleeves	FSHST401025

Online Resources

eCatalog

