

HFCDH Series Indoor Tight Buffer Hybrid, 2 strand, 2 16 AWG Conductor, Plenum, OS2, SM, Yellow Jacket

By Hubbell Premise Wiring

Catalog # [HFCDH002PS216](#)

HFCDH Series Indoor Tight Buffer Hybrid, 2 strand,2 16 AWG Conductor, Plenum, OS2, SM , Yellow Jacket

Features

- Corning ULTRA SMF-28® Singlemode Bend-Insensitive Optical Fiber
- E-Z Strip Buffer For Contractor-Friendly Termination
- 2 x 16 AWG Stranded Conductors for Distributed DC Power
- Pefect of Passive Optical Delivery

Application

Data Tranmission

Specifications

Industry Standard(s)TIA

Conductor

Number Of Fibers2

Fiber SizeSingle Mode

Fiber TypeOS2, SM

Current

Wavelength1310/1550 Nanometers

General

ColorYellow

UPC662620340647

TypeCable

Sub BrandFiber Optics

Material - JacketPVC

Cable RatingPlenum

Operational

Temperature Rating0 Degrees C to 70 Degrees C

Product Assets

[Catalog \[English\]](#)

[Catalog Page \[English\]](#)

