

HUBBELL
Premise Wiring

HFCH6 Series Indoor/Outdoor Loose Tube
6 strand, Riser, Armored, OM4, MM , Black
Jacket.

By Hubbell Premise Wiring
Catalog # [HFCH6006R4BK](#)

HFCH6 Series Indoor/Outdoor Loose Tube 6 strand, Riser,
Armored, OM4, MM , Black Jacket.

Features

- Multimode Bend-Insensitive Optical Fiber
- Loose Tube
- Durable Aluminum Interlock Armor
- Indoor/Outdoor
- Premium Fiber For Enhanced Optical Performance

Application

Data Transmission

Specifications

Industry Standard(s)	• ANSI/ICEA S-83-596 • NFPA-262/UL910/CSA FT-6 • Telcordia GR-409 • TIA-568.3-D
----------------------	---

Conductor

Number Of Fibers	6
------------------	---



Oh No!
IMAGE COMING SOON

Fiber Size	OM4
Fiber Type	OM4, MM
Current	
Wavelength	850/1300 Nanometers
General	
Color	Black
UPC	662620342689
Type	Cable
Sub Brand	Fiber Optics
Cable Rating	Riser, Armored
Logistics	
Carton Quantity	1000
Operational	
Bandwidth	4000 bps
Temperature Rating	-40 Degrees C to 70 Degrees C