

Category 6A Shielded Jack with Cobra-Lock™ Series Termination

By Hubbell Premise Wiring
Catalog # [HJS6AEI24](#)

Category 6A Shielded Jack with Cobra-Lock™ Termination



Features

- Third Party Verified Category 6A Component
- Cobra-Lock™ Termination Reduces Termination Time by Over 75%
- Wires Secured Under Constant Compression
- Easily Re-Terminate
- Qualified to 150% of 802.3bt PoE Current Level

Application

Up to 10GBASE-T, 802.3bt POE

Performance

TIA Cat 6A Component, Third Party Verified

Specifications

Industry Standard(s)	• ANSI/TIA/EIA-568 Category 6A component • UL 1863 - Communications-Circuit Accessory • IEC60512-99-002 POE Disconnection Endurance • UL 2043 - Suitable for Air-Handling Spaces • RoHS Compliant
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Contact	IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
---------	---

Current

Connectivity	RJ45 Jack to Cobra-Lock
Withstand Voltage	1,000 Vac @ 60 Hz

Dimensions

Size	0.87 (22) x 0.67 (17) x 1.39 (35)
------	-----------------------------------

Display Size

Standard Sized Product

General

Material - Housing	Diecast Zinc
Contact Point Material	Copper Alloy with Gold Over Plating
Specifications	• Wire Compatibility: 24-22 AWG Solid • Plug Compatibility:RJ-11 to 45
Color	Ivory
Style	RJ-45 Jack
Mounting Type	Snap-fit
UPC	662620666709
Type	Modular Jack with Cobra-Lock
Construction Material - Main	Diecast Zinc
Item Type	Modular Jack with Cobra-Lock
Sub Brand	Cobra-Lock
Series	Cobra-Lock™ Series

Logistics

Number of Pieces in Package	24
Carton Quantity	15

Operational

Operating Cycles	750+ Plug & 25 Re-Termination Cycles
Temperature Rating	Max Continuous- 75° C, Minimum- -40° C Without Impact

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Customer Drawing \[English\]](#)
- [Installation Manual \[English\]](#)