


HUBBELL
Premise Wiring

LGX Max Series CS Cassette, 36 Port, 18
Duplex CS to 3 MTP, OM3/OM4, Aqua

By Hubbell Premise Wiring
Catalog # [OCCSM34](#)



Fiber Optic High Density Cassette, LGX Standard Slot Size, 36 CS
to 3 MTP, OM3/OM4, Aqua

Features

- Utilizes the latest in Compact Duplex Connector Technology
- Fits in a standard LGX Slot
- Provides High fiber density in your current enclosure
- Provides Extreme high density in any size Enclosure
- Easy Access Pull Tab for Quick Disconnect

Application

Interconnect

Specifications

Industry Standard(s)	• Telcordia GR-326-CORE • TIA-568-C.3 • TIA-604-FOCIS
----------------------	---

Conductor

Number Of Fibers	36
Fiber Type	OM3/OM4

Configuration

Number Of Ports	18
-----------------	----

Current

Connectivity	Cassette
--------------	----------

Dimensions

Height	1.1 in
--------	--------

General

UPC	662620343877
-----	--------------

Logistics

Carton Quantity	50
-----------------	----

Operational

Adapter Type	CS Duplex
--------------	-----------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)