

OptiChannel
Fiber Accessory
Plug and Play Cassette

Features

- Compact Universal Design
- Designed for H4 Series 4 across Panels
- Quick and Easy Plug-n-Play Installation

Ordering Information

Description	Color	Catalog Number	UPC
Fiber Optic, Cassette Adapter Panel, High Density, H4 Opening, 40 Gig, LC to MTP, OM4, 8 Fiber, Violet	Violet	OCLCD40G8H4VI	662620606552

Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Specifications

Material	Ceramic
Fiber Size	250 Micron
Fiber Type	OM4
Style	LC-MTP
Polarity	Type A
Repeatability	0.1 dB
Service Life	500 matings
Temperature Rating	0 °C to 70 °C

Performance

Optical	
Total Insertion Loss	Less than 1.1dB (test data included)

HUBBELL

