

OptiChannel
Fiber Accessory
Plug and Play Cassette

Features

- Compact Universal Design
- Designed for H4 Series 4 Across Panels
- Quick and Easy Plug-n-Play Installation

Ordering Information

Description	Color	Catalog Number	UPC
Fiber Optic, Cassette Adapter Panel, High Density, H4 Opening, LC to MTP, OM4, 24 Fiber, Violet	Violet	OCLCQG4H4VI	662620606521

Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Specifications

Material	Ceramic
Fiber Size	250 Micron
Fiber Type	OM4
Style	LC Quad 24F
Polarity	Type A
Repeatability	0.1 dB
Service Life	500 matings
Temperature Rating	0 °C to 70 °C

Performance

Optical	
Total Insertion Loss	Less than 1.1dB (test data included)

HUBBELL

