

OptiChannel
Fiber Accessory
Plug and Play Cassette

Features

- Compact Universal Design
- Ten Gigabit Ethernet Assurance
- Quick and Easy Plug-n-Play Installation

Ordering Information

Description	Color	Catalog Number	UPC
Fiber Optic Cassette, LC-MT, OM2 Fiber, 125, 12-Fiber Strands, 10GHz, OM1 Fiber	Aqua	OCRJ50G	662620238012

Listings

Telcordia GR-326-CORE
TIA-568-C.3
TIA-604-FOCIS

Specifications

Material	Ceramic
Fiber Size	250 Micron
Fiber Type	OM3
Style	MT-RJ
Polarity	Type A
Repeatability	0.1 dB
Service Life	500 matings
Temperature Rating	0 °C to 70 °C

Performance

Optical

Total Insertion Loss	Less than 1.5dB (test data included)
----------------------	--------------------------------------

HUBBELL

