

Non-Metallic Raceway, BaseTrak Series, 2
Channel Base, 5' Length

By Hubbell Premise Wiring
Catalog # [PB2B5](#)



Non-Metallic Raceway, BaseTrak Series, 2 Channel Base, 5'
Length

Features

- UL Listed and CSA Certified to 600 volts
- Single and two channel latching raceways are dual-rated for both power and data applications, reducing inventory requirements

Application

5' Base

Performance

Environmental - Flame Rating - UL94V-0, Environmental -
Temperature Range - -25.6° to 158° F

Specifications

Non Hazardous Location	Non Hazardous
Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
EU RoHS Indicator	No

Configuration

Knockouts	None
-----------	------

Dimensions

Width	4.5 in
Length	5 ft

General

Item Type	PB2, 2-Channel BaseTrak
Construction	Extruded Plastic
Type	Base Only
Enclosure Type	NEMA 1 Rating
Series	PB2
Cover Type	Removable
Material	Thermoplastic
Specifications	• Crush Resistance - 300 lbs. • Impact Resistance - 5 ft. lbs. • Length - 5 ft. (1.5m) • Material - UV Stabilized PVC

UPC	783585310015
Style	Two Channel
Color	Office White

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)