

HUBBELL
Premise Wiring

Copper Solutions, Patch Cord, Cat6A,
10GHz, Shielded, Gray, 55' Length

By Hubbell Premise Wiring
Catalog # [PC6AGY55](#)

Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Gray, 55'
Length

Features

- Cat6A
- 10GHz
- Shielded
- Gray
- 55' Length

Application

Category 6A

Specifications

EU RoHS Indicator No

Conductor

Conductor Type Copper
Conductor Stranding Stranded
Number Of Conductors 8-Conductor



Wire Size	#24 AWG
Current	
Voltage Rating	300V AC kV
Dimensions	
Outside Diameter	0.218
General	
Color	Gray
UPC	662620215440
Plug Type	RJ45
Material - Jacket	Flame Redardant PVC
Material - Insulation	Flame Redardant PVC
OEM Brand Name	Hubbell Premise Wiring
Operational	
Temperature Rating	Per TIA