

HUBBELL
Premise Wiring

PC6AOR20

By Hubbell Premise Wiring
Catalog # [PC6AOR20](#)

Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, Orange,
20' Length



Application

Category 6A

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Conductor Stranding Stranded
Number Of Conductors 8-Conductor
Wire Size #24 AWG

Current

Voltage Rating 300V AC kV

Dimensions

Outside Diameter 0.218

General

Color Orange
UPC 662620204543
Plug Type RJ45
Material - Jacket Flame Redardant PVC
Material - Insulation Flame Redardant PVC

Logistics

Carton Quantity 50

Operational

Temperature Rating Per TIA