

HUBBELL
Premise Wiring

Copper Solutions, Patch Cord, Cat6A,
10GHz, Shielded, White, 7' Length

By Hubbell Premise Wiring
Catalog # [PC6AW07](#)

Copper Solutions, Patch Cord, Cat6A, 10GHz, Shielded, White, 7'
Length



Features

- Cat6A
- 10GHz
- Shielded
- White
- 7' Length

Application

Category 6A

Specifications

EU RoHS Indicator Yes

Conductor

Conductor Type Copper
Conductor Stranding Stranded
Number Of Conductors 8-Conductor
Wire Size #24 AWG

Current

Voltage Rating 300V AC kV

Dimensions

Outside Diameter 0.218

General

Color White
UPC 662620204437
Plug Type RJ45
Material - Jacket Flame Redardant PVC
Material - Insulation Flame Redardant PVC
OEM Brand Name Hubbell Premise Wiring

Logistics

Carton Quantity 100

Operational

Temperature Rating Per TIA

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)