

Non-Metallic Raceway, Latching
PremiseTrak, Adhesive Base and Cover, 5'
Length

By Hubbell Premise Wiring
Catalog # [PP1ABC5](#)

Non-Metallic Raceway Latching PremiseTrak, Adhesive Base and
Cover, 5'

Features

- UL Listed and CSA Certified to 600 volts
- Single and two channel latching raceways are dual-rated for both power and data applications, reducing inventory requirements

Application

5' Base and Cover- Adhesive Back

Performance

Environmental - Flame Rating - UL94V-0, Environmental -
Temperature Range - -25.6° to 158° F

Specifications

Non Hazardous Location	Non Hazardous
Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
EU RoHS Indicator	Yes

Configuration

Knockouts	None
-----------	------

Dimensions



Width	0.84 in
Length	5 ft
General	
Item Type	PP1, PremiseTrak 2- Latching
Construction	Extruded Plastic
Type	Base and Cover
Enclosure Type	NEMA 1 Rating
Series	PP1
Cover Type	Integral
Material	Thermoplastic
Specifications	• Crush Resistance - 300 lbs • Impact Resistance - 5 ft. lbs. • Length - 5 ft. (1.5m) • Material - UV Stabilized PVC
UPC	783585090443
Style	Single Channel, Latching
Color	Office White
Logistics	
Carton Quantity	100
Product Assets	
Catalog [English]	
Catalog [English]	
Catalog Page [English]	