

HUBBELL Premise Wiring

Non-Metallic Raceway, Latching PremiseTrak, Adhesive Base and Cover, 7' Length

By Hubbell Premise Wiring
Catalog # [PP1ABC7](#)

Non-Metallic Raceway, Latching PremiseTrak, Adhesive Base and
Cover, 7' Length

Features

- UL Listed and CSA Certified to 600 volts
- Single and two channel latching raceways are dual-rated for both power and data applications, reducing inventory requirements

Application

7' Base and Cover- Adhesive Back

Performance

Environmental - Flame Rating - UL94V-0, Environmental -
Temperature Range - -25.6° to 158° F

Specifications

Non Hazardous Location	Non Hazardous
Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E118895 / E119190• UL Standard UL 5A
EU RoHS Indicator	Yes

Configuration

Knockouts	None
-----------	------

Dimensions



Width	0.84 in
Length	7 ft

General

Item Type	PP1, PremiseTrak 2- Latching
Construction	Extruded Plastic
Type	Base and Cover
Enclosure Type	NEMA 1 Rating
Series	PP1
Cover Type	Integral
Material	Thermoplastic
Specifications	<ul style="list-style-type: none">• Crush Resistance - 300 lbs• Impact Resistance - 5 ft. lbs.• Length - 7 ft. (2.1m)• Material - UV Stabilized PVC

UPC	783585090450
Style	Single Channel, Latching
Color	Office White

Logistics

Carton Quantity	70
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)