

Non-Metallic Raceway, Latching
PremiseTrak, External Elbow

By Hubbell Premise Wiring
Catalog # [PP1EE](#)

Non-Metallic Raceway, Latching PremiseTrak, External Elbow



Features

- Full capacity 1¼ in. bend radius external elbow

Performance

Environmental - Flame Rating - UL94V-0, Environmental -
Temperature Range - -25.6° to 158° F

Specifications

Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
EU RoHS Indicator	Contact Manufacturer

General

Item Type	PP1 PremiseTrak (Latching) Series
-----------	--------------------------------------

Type	Elbows
Series	PP1
Material	Non-Metallic
Specifications	• Crush Resistance - 300 lbs. • Impact Resistance - 5 ft. lbs. • Material - UV Stabilized PVC
UPC	783585090528
Style	External
Color	Office White

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)