

Non-Metallic Raceway, Non-Latching
PremiseTrak, PREM-TRAK1, Base, Cover, 7'
Length

By Hubbell Premise Wiring
Catalog # [PT1BC7](#)

Non-Metallic Raceway, Non-Latching PremiseTrak, PREM-TRAK1,
Base, Cover, 7' Length

Features

- Office white color
- UL Listed and CSA Certified to 600 volts
- Single and two channel latching raceways are dual-rated for both power and data applications

Application

7' Base and Cover

Performance

Environmental - Flammability - UL94V-0, Environmental -
Operating Temperature - -25.6° to 158° F

Specifications

Non Hazardous Location	Non Hazardous
Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
EU RoHS Indicator	Yes
Standards - RoHS Compliance	CM
Status	

Configuration

Knockouts	None
-----------	------

Dimensions



Width	0.75 in
Length	7 ft

General

Item Type	PT1, PremiseTrak 1- Non Latching
Construction	Extruded Plastic
Type	Base and Cover
Enclosure Type	NEMA 1 Rating
Series	PT1
Cover Type	Integral
Material	Thermoplastic
Specifications	• Channel Area - 0.29 (sq. in.) • Crush Resistance - 300 lbs • Impact Resistance - 5 ft. lbs. • Material - UV Stabilized PVC
UPC	783585335827
Style	Single Channel
Color	Office White

Logistics

Carton Quantity	70
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)