

HUBBELL Premise Wiring

Non-Metallic Raceway, Portable-PlugTrak, 20A 3' Length, 5 Duplex, 6' Cord

By Hubbell Premise Wiring
Catalog # [PT203112P](#)

Non-Metallic Raceway Portable-PLUGTRAK 20A 3', 5-Duplex, 6'
Cord



Features

- Pre-punched holes make mounting easy
- Available in 3ft (0.9m) or 5ft (1.5m) lengths
- 6ft length, 15 or 20A molded cord set allows reliable access

Performance

Electrical - Crush Resistance - 300 lbs., Electrical - Impact Resistance - 5 ft. lbs, Electrical - Receptacle Rating - NEMA 5-15R & 5-20R, Environmental - Flame Rating - UL94V-0, Environmental - Temperature Range - -25.6° to 158° F, Mechanical - Wire - #12 AWG Stranded Copper

Specifications

Industry Standard(s)	<ul style="list-style-type: none">• CSA Standard C22.2 no. 62• E118895 / E119190• UL Standard UL 5A
EU RoHS Indicator	Contact Manufacturer

Conductor

Wire Size	#12 AWG THHN
-----------	--------------

Configuration

Number Of Receptacles	2
-----------------------	---

Current

Current / Amperage Rating	20 A
Voltage Rating	125 VAC

Dimensions

Length	3 ft
--------	------

General

Item Type	Portable PlugTrak
Type	Single Circuit
Series	Non-Metallic
Specifications	<ul style="list-style-type: none">• Cord Length - 6 (ft.)• Material - UV Stabilized PVC• Number of Receptacles - 2 Duplex• PlugTrak Amperage - 20A• PlugTrak Length - 3 Foot• Receptacle Face - Thermoplastic
UPC	783585091280
Style	Portable
Color	Office White

Logistics

Carton Quantity	2
-----------------	---

Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)