

# HUBBELL Premise Wiring

## Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK, 5', 20A 125V, 2-Circuit, 5 Duplex

By Hubbell Premise Wiring  
Catalog # [PT205212](#)

Non-Metallic Raceway, Non-Metallic PlugTrak Series, PLUGTRAK,  
5', 20A 125V, 2-Circuit, 5 Duplex

### Features

- Available in 5 ft. or 6 ft. lengths
- Multiple spacing configurations
- Hard wired PlugTrak® mates with LANTrak® fittings and boxes

### Performance

Electrical - Crush Resistance - 300 lbs., Electrical - Impact Resistance - 5 ft. lbs, Electrical - Receptacle Rating - NEMA 5-15R & 5-20R, Environmental - Flame Rating - UL94V-0, Environmental - Temperature Range - -25.6° to 158° F, Mechanical - Wire - #12 AWG Stranded Copper

### Specifications

Industry Standard(s)	<ul style="list-style-type: none"><li>• CSA Standard C22.2 no. 62</li><li>• E118895 / E119190</li><li>• UL Standard UL 5A</li></ul>
EU RoHS Indicator	Contact Manufacturer

### Conductor

Wire Size	#12 AWG THHN
-----------	--------------

### Configuration

Number Of Receptacles	5
-----------------------	---

### Current

Current / Amperage Rating	20 A
Voltage Rating	125 VAC



### Dimensions

Length	5 ft
--------	------

### General

Item Type	Pre-Wired PlugTrak
Type	Two Circuits
Series	Non-Metallic
Specifications	<ul style="list-style-type: none"><li>• Material - UV Stabilized PVC</li><li>• Number of Receptacles - 5 Duplex</li><li>• PlugTrak Amperage - 20A</li><li>• PlugTrak Length - 5 Foot</li><li>• Receptacle Face - Thermoplastic</li><li>• Spacing - 12 Inch</li></ul>
UPC	783585091044
Style	Standard
Color	Office White

### Logistics

Carton Quantity	10
-----------------	----

### Product Assets

- [Catalog \[English\]](#)
- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)