

Fire-Rated Poke-Throughs Multi-Service Painted Pedestal 3 Inch Core Hole Unit

HUBBELL®

Features

- 1–4 hour fire rating
(1–3 hour for steel floor units and concrete topping, D900 Series Design)
- For 2 1/4 in. to 7 in. floor thickness
- Approved for use in the City of Chicago

Ordering Information

Description	UPC	Catalog Number
Large Capacity Multi-Service Pedestal Through-Floor Fitting with (1) 1 1/4 in. EMT stem for low voltage and (1) 1/2 in. EMT stem for power applications.	783585204475	PT7XC

Listings

cULus Listed
Fire Resistance - R8429
Outlet Box- E31999

Specifications

Material	Composite
----------	-----------

Electrical

Power Wiring Capacity	Up to ten #12 AWG type THHN wires, or Up to six #12 AWG and two #10 AWG type THHN wires
Voice/Data Wiring Capacity	Up to four 25 pair tel./data cables (200 #22 AWG tel./data conductors), or Up to five IBM Type 2 data cables

Mechanical

Max. Cu Cross Section	1/2" Power EMT .0461 sq. in., 1 1/2" Low Voltage EMT .1000 sq. in.
UL Spacing Restrictions	Min. of 2 ft. O.C. and not more than one unit per each 65 sq. ft. of floor area in each span

Related Product

Pedestal Service Fitting	FR80AL
6-Gang Pedestal Service Fitting	FR680GYA
4-Gang Pedestal Service Fitting	FR480GYA
2-Gang Pedestal Service Fitting	FR280GYA



Links

[ecatalog](#)
[Media](#)