

inSIGHT™ Data Com Rack Power Distribution Unit

Basic Power Distribution

Complete line of single and three phase PDUs

HUBBELL

Features

- Locking standard cords to prevent inadvertent disconnection
- High reliability with robotically soldered connections
- Available in Black, Blue, Red, and White

Ordering Information

| Type                     | Nominal          | Catalog Number | UPC          |
|--------------------------|------------------|----------------|--------------|
| Basic always on powering | 208V Three Phase | PV72BD50GD-6RD | 662620365886 |

Listings

UL 2416  
EIA 310-E Universal Mounting Pattern  
UL 60950-1

Specifications

|                        |                                    |
|------------------------|------------------------------------|
| Input Current (A)      | 50 Amp                             |
| Input Power Cord       | CS8365C Plug                       |
| Receptacle group       | 36 C13 & 6 C19 Receptacle          |
| PDU Size               | 72" vertical mount                 |
| Regulatory Approval    | TUV Certified to UL / CSA 609050-1 |
| Operating Environment  | 0 to 60                            |
| Storage Environment    | -25 to 65                          |
| PDU Dimension (inches) | 72 length X 2.2 width X 4.8 depth  |

Performance

Low profile

2.18" X 2"

Receptacle Locking

Secured with standard cords

Online Resources

eCatalog

