

inSIGHT™ Data Com Rack Power Distribution Unit

Basic Power Distribution

Complete line of single and three phase PDUs

HUBBELL

Features

- Locking standard cords to prevent inadvertent disconnection
- High reliability with robotically soldered connections
- Available in Black, Blue, Red, and White

Ordering Information

Type	Nominal	Catalog Number	UPC
Basic always on powering	415V Three Phase	PV72BE30HH-6RD	662620367002

Listings

UL 2416
EIA 310-E Universal Mounting Pattern
UL 60950-1

Specifications

Input Current (A)	30 Amp
Input Power Cord	IEC 60309 / IP 44 Plug
Receptacle group	30 C13 & 12 C19 Receptacle
PDU Size	72" vertical mount
Regulatory Approval	TUV Certified to UL / CSA 609050-1
Operating Environment	0 to 60
Storage Environment	-25 to 65
PDU Dimension (inches)	72 length X 2.2 width X 4.8 depth

Performance

Low profile

2.18" X 2"

Receptacle Locking

Secured with standard cords

Online Resources

eCatalog

