

inSIGHT™ Data Com Rack Power Distribution Unit

Basic Power Distribution

Complete line of single and three phase PDUs



Features

- Locking standard cords to prevent inadvertent disconnection
- High reliability with robotically soldered connections
- Available in Black, Blue, Red, and White



Ordering Information

| Type                     | Nominal          | Catalog Number | UPC          |
|--------------------------|------------------|----------------|--------------|
| Basic always on powering | 415V Three Phase | PV72BE60HI-6BL | 662620367101 |

Listings

UL 2416  
EIA 310-E Universal Mounting Pattern  
UL 60950-1

Specifications

|                        |                                    |
|------------------------|------------------------------------|
| Input Current (A)      | 60 Amp                             |
| Input Power Cord       | IEC 60309 / IP 44 Plug             |
| Receptacle group       | 27 C19 Receptacle                  |
| PDU Size               | 72" vertical mount                 |
| Regulatory Approval    | TUV Certified to UL / CSA 609050-1 |
| Operating Environment  | 0 to 60                            |
| Storage Environment    | -25 to 65                          |
| PDU Dimension (inches) | 72 length X 2.2 width X 4.8 depth  |

Performance

Low profile

2.18" X 2". Improves airflow

Receptacle Locking

Prevents inadvertent disconnections. Secured with standard cords

Online Resources

eCatalog

