

inSIGHT™ Data Com Rack Power Distribution Unit  
Intelligent Power Distribution  
Complete line of single and three phase  
intelligent PDUs



Features

- Includes Advanced Monitoring on LCD screen and web browser
- Locking standard cords to prevent inadvertent disconnection
- Up to four environmental sensors per PDU that measures temperature and humidity
- Monitored and switch enabled - Use Switching cords for equipment switching capability.
- Available in Black, Blue, Red, and White

Ordering Information

| Type         | Nominal           | Catalog Number | UPC          |
|--------------|-------------------|----------------|--------------|
| Switch Ready | 208V Single Phase | PV72IB30DD-6BL | 662620365213 |

Listings

UL 2416  
EIA 310-E Universal Mounting Pattern  
UL 60950-1  
SNMP V3

Specifications

|                        |                                      |
|------------------------|--------------------------------------|
| Input Current (A)      | 30 Amp                               |
| Input Power Cord       | L6-30P Plug                          |
| Receptacle group       | 36 C13 & 6 C19 Receptacle            |
| PDU Size               | 72" vertical mount                   |
| Regulatory Approval    | TUV Certified to UL / CSA 609050-1   |
| Operating Environment  | 0 to 60                              |
| Storage Environment    | -25 to 65                            |
| PDU Dimension (inches) | 72 length X 2.2 width X 4.8 depth    |
| Network Interface      | Dual Ethernet RJ-45, 10/100 Mbit/sec |

Performance

Intelligence

Remote & touch screen display

Low profile

2.18" X 2". Improves airflow

Receptacle Locking

Prevents inadvertent disconnections. Secured with standard cords

Touch and Rotate Digital Display

Touch to view / rotate. Optional sensor -daisy chain up to four for temp/humidity

Accessories

|                                                            |                |
|------------------------------------------------------------|----------------|
| One Sensor (A) and 6 foot connecting cord                  | PENVPODA       |
| Two Sensors (A, B) and two 6 foot connecting cord          | PENVPODAB      |
| Three Sensors (A, B, C) and three 6 foot connecting cords  | PENVPODABC     |
| Four sensors (A, B, C, D) and four 6 foot connecting cords | PENVPODABCD    |
| Environmental sensor 6 foot connecting cord                | PENV6FTCORD    |
| Environmental sensor 9 foot connecting cord                | PENV9FOOTCORD  |
| Outlet Switching and Metering, C13-C14, 5 foot             | PSWCRDC1314-05 |
| Outlet Switching & Metering, C19-C20, 5 foot               | PSWCRDC1920-05 |

Online Resources

eCatalog



Hubbell Premise Wiring