

inSIGHT™ Data Com Rack Power Distribution Unit
Intelligent Power Distribution
Complete line of single and three phase
intelligent PDUs



Features

- Includes Advanced Monitoring on LCD screen and web browser
- Locking standard cords to prevent inadvertent disconnection
- Up to four environmental sensors per PDU that measures temperature and humidity
- Monitored and switch enabled - Use Switching cords for equipment switching capability.
- Available in Black, Blue, Red, and White

Ordering Information

Type	Nominal	Catalog Number	UPC
Switch Ready	208V Three Phase	PV72ID50GD-6BL	662620365855

Listings

UL 2416
EIA 310-E Universal Mounting Pattern
UL 60950-1
SNMP V3

Specifications

Input Current (A)	50 Amp
Input Power Cord	CS8365C Plug
Receptacle group	36 C13 & 6 C19 Receptacle
PDU Size	72" vertical mount
Regulatory Approval	TUV Certified to UL / CSA 609050-1
Operating Environment	0 to 60
Storage Environment	-25 to 65
PDU Dimension (inches)	72 length X 2.2 width X 4.8 depth
Network Interface	Dual Ethernet RJ-45, 10/100 Mbit/sec

Performance

Intelligence

Remote & touch screen display

Low profile

2.18" X 2". Improves airflow

Receptacle Locking

Prevents inadvertent disconnections. Secured with standard cords

Touch and Rotate Digital Display

Touch to view / rotate. Optional sensor -daisy chain up to four for temp/humidity

Accessories

One Sensor (A) and 6 foot connecting cord	PENVPODA
Two Sensors (A, B) and two 6 foot connecting cord	PENVPODAB
Three Sensors (A, B, C) and three 6 foot connecting cords	PENVPODABC
Four sensors (A, B, C, D) and four 6 foot connecting cords	PENVPODABCD
Environmental sensor 6 foot connecting cord	PENV6FTCORD
Environmental sensor 9 foot connecting cord	PENV9FOOTCORD
Outlet Switching and Metering, C13-C14, 5 foot	PSWCRDC1314-05
Outlet Switching & Metering, C19-C20, 5 foot	PSWCRDC1920-05

Online Resources

eCatalog



Hubbell Premise Wiring