

Non-Metallic Raceway, Latching
PremiseTrak, Wall-TRAK1, Base, Cover, 7'
Length

By Hubbell Premise Wiring
Catalog # [PW1BC7](#)

Non-Metallic Raceway Latching PremiseTrak, Wall-TRAK1,Base,
Cover, 7'

Features

- UL Listed and CSA Certified to 600 volts
- Single and two channel latching raceways are dual-rated for both power and data applications, reducing inventory requirements

Application

7' Base and Cover

Performance

Environmental - Flame Rating - UL94V-0, Environmental -
Temperature Range - -25.6° to 158° F

Specifications

Non Hazardous Location	Non Hazardous
Industry Standard(s)	• CSA Standard C22.2 no. 62 • E118895 / E119190 • UL Standard UL 5A
EU RoHS Indicator	Yes

Configuration

Knockouts	None
-----------	------

Dimensions

Width	1.19 in
-------	---------



Length	7 ft
General	
Item Type	PW1, WallTrak- Latching
Construction	Extruded Plastic
Type	Base and Cover
Enclosure Type	NEMA 1 Rating
Series	PW1
Cover Type	Removable
Material	Thermoplastic
Specifications	• Crush Resistance - 300 lbs. • Impact Resistance - 5 ft. lbs. • Length - 7 ft. (2.1m) • Material - UV Stabilized PVC
UPC	783585092010
Style	Single Channel, Latching
Color	Office White

Logistics

Carton Quantity	70
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Catalog Page \[English\]](#)