

HUBBELL Premise Wiring

15A Kitchen Counter Receptacle, Surface Mount, Brass

By Hubbell Premise Wiring
Catalog # [RCT200BR](#)

15A Kitchen Counter Receptacle, Surface Mount, Brass



Features

- Spill water tested
- UL Listed for countertop installation.
- Permanent installation ready (suitable for MC cable or non-metallic sheath cable)
- Push down to pop-up function is rated for a minimum of 10,000 cycles
- Easy installations - simply drop in and tighten.

Application

Power on Counter Top

Specifications

Industry Standard(s)	UL
EU RoHS Indicator	Contact Manufacturer
Nema Rating	5-15R

Conductor

Number Of Wires	3
Number Of Poles	2

Current

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Dimensions

Width	4.20 in
Height	6.48 in
Length	4.20 in
Dimensions	4.20 in x 4.20 in x 6.48 in

General

Construction Material - Main	200 Meunt
Sub Brand	Under Counter Boxes
Construction	Fabricated
Type	Power Only
Series	Countertop Receptacle
Material	200 Meunt
UPC	883778307959
Style	Surface
Color	Brass

Logistics

Carton Quantity	10
Pallet Quantity	630

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[French, English\]](#)