

Recessed 6" Series, Through Floor Fitting
Only, No Sub Plates, No Junction Box

By Hubbell Premise Wiring
Catalog # [SIR6PTFITCHI](#)

Recessed 6" Series, Through Floor Fitting Only, No Sub Plates,
No Junction Box

Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

6" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s)	cULus Listed
EU RoHS Indicator	Contact Manufacturer

Conductor

Cable Entry	Through Cover
-------------	---------------

Dimensions

Size	Standard Sized Product
------	------------------------

General

Sub Brand	SystemOne Recessed
-----------	--------------------



Type	6" Recessed Rated Poke Through Only
Material	Fabricated
Specifications	• Fire Resistance Rating - 2-Hrs. (D900) • Floor thickness - 2 1/4 in. (57.2) • Max. Cu Cross Section - 3/4 in. Power EMT .0307 sq. in. • Mounting - 6 in. (152.4)
UPC	783585443195
Style	FRPT Kits
Application - For Use On	Concrete
Color	Metallic
Mounting Type	6" Core Hole

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)