

HUBBELL
Premise Wiring

Recessed 6" Series, Sub Plate, 50% Right Side, (3) 20A Pre-Wired Tamper Resistant Receptacles, 1 Circuit, 18" Leads

By Hubbell Premise Wiring
Catalog # [S1R6SP3RTR](#)

Recessed 6" Series, Sub Plate, 50% Right Side, (3) 20A Pre-Wired Tamper Resistant Receptacles, 1 Circuit, 18" Leads

Features

- Steel Construction
- White Powder Coat Paint
- Includes IG and CONTROLLED Stickers and Necessary Mounting Hardware

Application

6" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s)	cULus Listed
EU RoHS Indicator	Contact Manufacturer

Conductor

Cable Entry	Through Cover
-------------	---------------

Configuration

Number Of Outlets	(3) 20A Pre-Wired Tamper Resistant Receptacles, 1 Circuit, 18" Leads
-------------------	--



General

Application - For Use On	Concrete
Color	White
Style	Sub-Plates
Mounting Type	Screw Mount
UPC	783585696485
Type	6" Recessed Rated Poke Through Sub Plates
Material - Mounting Hardware	Mounting Hardware Included
Sub Brand	SystemOne Recessed
Material	Fabricated

Logistics

Carton Quantity	12
-----------------	----

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English, Spanish, French\]](#)