

HUBBELL

Premise Wiring

Recessed 8" Series, Through Floor Fitting Only, (1) S1R8JNC1 fitting box, No S1FRPTJB, No Flexible Metal Conduit, No Sub Plates

By Hubbell Premise Wiring
Catalog # [S1R8PTFIT1CHI](#)

Recessed 8" Series, Through Floor Fitting Only, (1) S1R8JNC1 fitting box, No S1FRPTJB, No Flexible Metal Conduit, No Sub Plates

Features

- For use with a 8.00" to 8.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

8" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s)	• cULus Listed • UL 514A Listed
EU RoHS Indicator	Contact Manufacturer

Conductor

Cable Entry	Through Cover
-------------	---------------



Dimensions

Size	Standard Sized Product
------	------------------------

General

Sub Brand	SystemOne Recessed
Type	8" Recessed Rated Poke Through Kit
Material	Fabricated
Specifications	Floor thickness - 2 1/4 in. (57.2)
UPC	783585443904
Style	FRPT Fittings
Application - For Use On	Concrete
Mounting Type	8" Core Hole

Product Assets

[Catalog \[English\]](#)
[Catalog \[English\]](#)
[Catalog Page \[English\]](#)