

HUBBELL
Premise Wiring

Recessed 8" Series, Through Floor Fitting
Only, (1) S1R8JNC3 fitting box, No
S1FRPTJB, No Flexible Metal Conduit, No
Sub Plates

By Hubbell Premise Wiring
Catalog # [S1R8PTFIT3CHI](#)

Recessed 8" Series, Through Floor Fitting Only, (1) S1R8JNC3
fitting box, No S1FRPTJB, No Flexible Metal Conduit, No Sub
Plates

Features

- For use with a 8.00" to 8.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

8" Fire-Rated Poke-Through Series

Specifications

Industry Standard(s)	• cULus Listed • UL 514A Listed
EU RoHS Indicator	Contact Manufacturer

Conductor

Cable Entry	Through Cover
-------------	---------------

Dimensions



Size	Standard Sized Product
General	
Sub Brand	SystemOne Recessed
Material - Mounting Hardware Type	Mounting Hardware Included 8" Recessed Rated Poke Through Kit
Material	Fabricated
Specifications	Floor thickness - 2 1/4 in. (57.2)
UPC	783585443928
Style	FRPT Fittings
Application - For Use On	Concrete
Mounting Type	8" Core Hole
Product Assets	
Catalog [English]	
Catalog [English]	
Catalog Page [English]	