

Double Ended Cobra-Lock™ Series Coupler

By Hubbell Premise Wiring
Catalog # [SC6A](#)

Double Ended Cobra-Lock™ Coupler



Features

- Preterminated to Cat 6A FTP bootless Patch Cord
- Cobra-Lock™ Termination Provides Speed and Reliability
- Provided with Mount-Anywhere Clip
- Cat 6A Channel Compliant
- Built From Plenum Rated Components

Application

Up to 10GBASE-T, 802.3bt POE

Performance

TIA Cat 6A Channel Compliant

Specifications

Industry Standard(s)	• ANSI/TIA/EIA-568 Category 6A channel • UL 1863 - Communications-Circuit Accessory • UL 2043 - Suitable for Air-Handling Spaces • RoHS Compliant
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
EU RoHS Indicator	Yes

Conductor

Contact	IDC: Phosphor Bronze with 100 Micro-Inch Tin Over Plating
---------	---

Current

Connectivity	Cobra-Lock to Cobra-Lock
Withstand Voltage	1,000 Vac @ 60 Hz

Dimensions

Size	0.92 (23) x 0.66 (17) x 1.65 (42)
Display Size	Standard Sized Product

General

Material - Housing Specifications	Diecast Zinc • Housing - Zinc Diecast • IDC Contact - Phosphor bronze with 100 micro-inch tin plating over nickel under plating
Color	Silver
Style	Cobra-Lock Coupler Accessory
Mounting Type	Mount Anywhere Clip
UPC	662620344263
Type	Coupler
Construction Material - Main Item Type	Diecast Zinc Coupler
Sub Brand	Cobra-Lock
Series	Cobra-Lock™ Series

Logistics

Number of Pieces in Package	1
Carton Quantity	24

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[English\]](#)